

Accessories for Special Communication Portfolio

K7431348

Properties



Ports

Interface	Gender
7/16	jack (female)
7/16	jack (female)
7/16	jack (female)

Electrical bands

	Signal band 1
Frequency range	38 GHz ... 0.512GHz
Insertion loss	0.05 dB
Composit power max	1000 W

Electrical Data (impedance)

Characteristic impedance	50 Ω
--------------------------	------

Mechanical data

Width	82 mm
Height	409 mm
Depth	82 mm
Housing material and surface treatment	Aluminium / Passivated

Environmental data

Environment (application)	Indoor/Outdoor
---------------------------	----------------

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.