

Accessories for Special Communication Portfolio
K7431358

Properties



Ports		
Port designation	Interface	Gender
Input 1	7/16	jack (female)
Output 1	7/16	jack (female)
Output 2	7/16	jack (female)
Output 3	7/16	jack (female)
Output 4	7/16	jack (female)

Electrical bands	
	Signal band 1
Frequency range	38 GHz ... 0.512GHz
Insertion loss	0.05 dB
Composit power max	1000 W

Electrical Data (impedance)	
Characteristic impedance	50 Ω

Mechanical data	
Width	82 mm
Height	409 mm
Depth	82 mm
Housing material and surface treatment	Aluminium / Passivated

Environmental data	
Environment (application)	Indoor/Outdoor

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

Accessories for Special Communication Portfolio
K7431358

DOCUMENT PIM-P1025 / Date of publication: 09.11.2023 / uncontrolled copy