

RG_223_/U-60

RG_223_/U-60

Properties

Construction			
Component	Material	Detail	Diameter
Centre conductor	Copper, Silver plated	Wire, 96%	0.88 mm
Dielectric	PE (Polyethylene)		2.95 mm
Outer conductor	Copper, Tin plated	Braid, 96%	3.6 mm
Outer conductor	Copper, Tin plated	Braid, 94%	4.2 mm
Jacket	PVC (Polyvinyl chloride)	RAL 7032 - gr	5.4 mm +/- 0.1 mm

Environmental data	
Fire characteristics	contains halogene

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22511565	RoHS 2011/65/EU and (EU) 2015/863	Compliant without exemption	
	REACH 1907/2006 Article 33 SVHC	Free of SVHC >0,1%	

Ordering information	
Item number	Item description
22511565	RG_223_/U-60

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37947 / Date of publication: 11.03.2026 / uncontrolled copy