TWAF-1130

TWAF-91630

The full head Torque Wrenches behave like traditional open end wrenches. Designed for "F" Connectors, these wrenches help prevent over tightening. An audible click tells you the F Connector has been torqued to the proper torque requirement. These wrenches all have angle heads, sized for 1/2", 7/16", 9/16" applications, and are designed with an ergonomic cushioned handle for user comfort and protection. These wrenches work in tightening mode only.
Note: Speed wrenches are designed to act like a ratcheting wrench, skipping over corners of nuts/bolts (allowing for continuous turning).

SPECIFICATIONS	TWAF-1130	TWAF-1220	TWAF-71620	TWAF-71625	TWAF-71630	TWAF-71640	TWAF-91620	TWAF-91630	TWAF-91640	TWAS-71620	TWAS-71630
HEAD TYPE	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Full-Size Open Head	Speed	Speed
TORQUE	30 inch-lbs (3.39 N-m)	20 inch-lbs (2.26 N-m)	20 inch-lbs (2.26 N-m)	25 inch-lbs (2.82 N-m)	30 inch-lbs (3.39 N-m)	40 inch-lbs (4.52 N-m)	20 inch-lbs (2.26 N-m)	30 inch-lbs (3.39 N-m)	40 inch-lbs (4.52 N-m)	20 inch-lbs (2.26 N-m)	30 inch-lbs (3.39 N-m)
SIZE	7/16" F Connectors & 11mm Nuts and Bolts	1/2" (12.7mm)	7/16" (11.11mm)	7/16" (11.11mm)	7/16" (11.11mm)	7/16" (11.11mm)	9/16" (14.29mm)	9/16" (14.29mm)	9/16" (14.29mm)	7/16" (11.11mm)	7/16" (11.11mm)
HEAD ANGLE	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees	15 Degrees
LENGTH	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)
MATERIAL	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel	High Carbon Alloy Steel
FINISH	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide	Black Oxide
HANDLE	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip	Ergonomic Cushion Grip
COLOR	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle	Blue Handle
WEIGHT	0.36 lbs (163g)	0.35 lbs (158.76g)	0.36 lbs (163g)	0.36 lbs (163g)	0.36 lbs (163g)	0.36 lbs (163g)	0.37 lbs (167.82g)	0.37 lbs (167.82g)	0.37 lbs (167.82g)	0.35 lbs (158.76g)	0.35 lbs (158.76g)
UPC NO.	811490019560	811490016453	811490010635	811490019379	811490010642	811490015210	811490016446	811490016576	811490018815	811490010659	811490010666

Tel 914.793.0700 | Fax 914.793.4527 | jonard.com