



AVERY DENNISON MARKETING SPECIFICATION

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

HISTORY		
REV.	DATE	DESCRIPTION
A	06.23.09	RELEASE TO PRODUCTION



DETAIL A: MOUNTING SLOT

MOUNTING:	SEE DETAIL A
TENSILE STRENGTH:	50 LBF / 222 N MIN.
TEMPERATURE RANGE:	-40 °F (-40 °C) TO 239 °F (115 °C) CONTINUOUS AND 257 °F (125 °C) AT MAXIMUM EXPOSURE
WEIGHT:	2.00 GRAMS
BUNDLE DIAMETER:	Ø 1.6MM TO Ø 44.5MM
TOOL:	12001 - HAND INSTALLATION TOOL 12500 - PNUEM. INSTALLATION TOOL
TOOL TENSION SETTING:	6 - 8
PACKAGING:	500/BAG, 10 BAGS/MASTER

APPROVALS:	ENG. APPR. <i>Daniel J. Stoen</i> 7/15/09	Q.A. APPR. <i>Edwin M. Stoen</i> 7-15-09	AVERY DENNISON FASTENER DIVISION FITCHBURG, MA 01420 U.S.A. TEL: 1-800-225-5913 FAX: 978-353-8157
SPECIFIED TOLERANCES ARE:	.XX ± .03 IN. .XXX ± .010 IN.	MATERIAL NYLON 6/6 IMPACT MODIFIED, HEAT STABILIZED COLOR BLACK	DESCRIPTION ADFM CONNECTOR TIE STOCK NO. 20124
	.X ± .7 MM .XX ± .25 MM	REV. A	