



2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number



Part Number Builder

<input type="text"/>	-	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
Series		No. of Port	No. of Positions Contacts	Shield Option	Option

**Series**

G8X - RJ45 Modular Jack with 10/100 magnetics and POE

**Number of Ports**

1 - 1 Port

**Number of Positions / Contacts**

88 - 8 Positions / 8 Contacts

**Shield Options**

S7 - Shielded

**Magnetics Package**

BP - 10/100 with POE

Contact Kycon for Schematics Options

**MODULAR JACKS WITH MAGNETICS:  
G8X Series**

RJ45 Modular Jack with 10/100 magnetics and POE

**Product Features**

- Includes magnetics to support 10/100 Base-T applications
- POE compatible
- LEDs for status indicators
- Shielded for EMI suppression
- PCB guide pegs

**Performance Specifications**

**Materials and Finish**

**Housing Material**

PBT Thermoplastic, UL 94V-0 Rated, Black Color

**Shield Material**

Brass, Nickel Plated

**Contact Material**

Phosphor Bronze

**Plating**

Nickel Underplating, 6µ" Gold Plate on Contact Area, Tin Plated on Solder Area

**Electrical Characteristics**

**Insulation Resistance**

500 Megohms Min.

**Contact Resistance**

20 milliohms Max.

**Dielectric Withstanding Voltage**

1200V AC for 1 Minute

**Mechanical Characteristics**

**Durability Rating**

750 Cycles Min.

**Mating Force**

30 N Max.

**Operating Temperature**

-40°C to +85°C

**Storage Temperature**

-40°C to +85°C

**G8X Series**

Dimensions in mm

