



AUDIO JACKS: STX-3542 Series

3.5mm, Audio Jack, SMT, 5 Pole

Product Features

5-Pole contact, TRRRS
Provides enough contacts for: Active Noise Canceling,
Balanced Audio and Biaural Recordings
Complies with EIA Standards

Performance Specifications

Materials and Finish

Housing

High Temperature Thermoplastic, UL 94V-0 Rated
Color: Black

Contact Material

Phosphor Bronze, Gold Plated

Electrical Characteristics

Insulation Resistance

100 Megohms at 500V DC

Contact Resistance

30 milliohms Max.

Dielectric Withstanding Voltage

500V AC RMS for 1 Minute

Mechanical Characteristics

Insertion Force: 0.4kg - 3.0kg

Withdrawal Force: 0.3kg - 3.0kg

Durability: 5,000 Mating Cycles

Operating Temperature

-25°C to + 70°C

Mating Connectors

STX-P-5POLE

2D Drawing

IGES

STEP

3D PDF

Solder Profile

CofC RoHS Compliant

CofC REACH Compliant

UL Plastic File

Certificate of Origin

Check Stock

Request a Sample

Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Number of Pins	Threading Option	Plating	Packaging

Series

STX-3542- 3.5mm Audio Jack

Number of Pins

5 - 5 Pins, 5 Pole

Threading Option

N - Non-Threaded Barrel

Plating

G - Gold plated

Packaging

TR - Tape and Reel

Contact Kycon for other options

STX-3542-5N-G-TR

Dimensions in mm

