



Tolerances:
All dimensions +/- .125"


STORAGE CONTAINERS

• These items made to order

Item No.	REF#	Box Size I.D. - L x W x D	Handles	Lid	Wire	Foam
37508	411-BX	16-7/8 x 10 x 3-1/2 IN (429 x 254 x 89 MM)	N/A	37550	N/A	37451
37501	401-BX	16-7/8 x 10 x 5-3/8 IN (429 x 254 x 137 MM)	N/A	37550	N/A	37451
37509	422-BX	17 x 9-7/8 x 2-1/2 IN (432 x 254 x 137 MM)	N/A	37550	N/A	37451
37500	400-BX	17 x 9-7/8 x 7-1/4 IN (432 x 251 x 184 MM)	37450	37550	N/A	37451
37512	438-BX	17 x 13 x 8-3/4 IN (432 x 330 x 222 MM)	37450	37551	37456	37452
37520 •	456-BX	18-3/8 x 12-3/8 x 6-3/4 IN (467 x 314 x 171 MM)	37450	37553	37458	37454
37505	405-BX	18-1/2 x 12-3/8 x 18-3/4 IN (470 x 314 x 476 MM)	37450	37553	37458	37454
37506	406-BX	18-5/8 x 15 x 5-7/8 IN (473 x 381 x 149 MM)	37450	37554	37459	37455
37527	468-BX	18-5/8 x 15 x 8 IN (473 x 381 x 203 MM)	37450	37554	37459	37455
37524	460-BX	18-5/8 x 15 x 10 IN (473 x 381 x 254 MM)	37450	37554	37459	37455
37525	462-BX	18-5/8 x 15 x 12 IN (473 x 381 x 305 MM)	37450	37554	37459	37455
37526	464-BX	18-5/8 x 15 x 14 IN (473 x 381 x 356 MM)	37450	37554	37459	37455
37516	446-BX	22-7/8 x 12-7/8 x 6 IN (581 x 327 x 152 MM)	37450	37552	37457	37453
37517	448-BX	22-7/8 x 12-7/8 x 8 IN (581 x 327 x 203 MM)	37450	37552	37457	37453
37514	440-BX	22-7/8 x 12-7/8 x 10 IN (581 x 327 x 254 MM)	37450	37552	37457	37453
37504	404-BX	22-7/8 x 12-7/8 x 12-5/8 IN (581 x 327 x 321 MM)	37450	37552	37457	37453
37515	445-BX	22-7/8 x 12-7/8 x 15-1/4 IN (581 x 327 x 387 MM)	37450	37552	37457	37453
37530		21-7/8 x 18-7/8 x 4-1/4 IN (556 x 479 x 108 MM)	N/A	37557	N/A	N/A
37532		22 x 18-7/8 x 8 IN (559 x 480 x 203 MM)	N/A	37557	NA	N/A



Conductive Plastic
Handles



Permanently static dissipative
crosslink bottom foam to
cushion circuit boards



Steel wire perimeter
reinforcing frame for extra
strength and durability