

# Product data sheet

## Characteristics

### 7XB4N

Limit switch lever, 9007, 9007MS/ML zinc, fixed length, inside nylon roller



#### Main

Range of Product	9007
Series name	Miniature potted
Product or Component Type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 2 in (50.80 mm) -
Type of roller	1 nylon inside roller 0.75 in (19.05 mm) 0.5 in (12.70 mm)
Type of approach	Lateral approach
Positive opening	Without

#### Complementary

Tracks	0.875 in
Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

#### Environment

Ambient Air Temperature for Operation	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Environmental characteristic	Standard environment

#### Ordering and shipping details

Category	22421-LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	785901609896
Nbr. of units in pkg.	1
Package weight(Lbs)	1.60 oz (45.359 g)
Returnability	No
Country of origin	MX

#### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.54 in (6.452 cm)
Package 1 width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)

#### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

## Contractual warranty

---

Warranty	18 months
----------	-----------

---