

9001KS47B

Selector switch head, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, stay put



Main

Bezel material	Metal
Device short name	K
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Product or Component Type	Head for selector switch
Range of Product	Harmony 9001K

Complementary

Cap/operator or lens colour	black
Contacts type and composition	Without contact block
Operator position information	3 positions
Operator profile	Standard handle
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Maintained

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901384472
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	4.32 oz (122.47 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------