



Main

Range of Product	Harmony 9001K
Product or Component Type	Head for push-to-test pilot light
Device short name	K

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Cap/operator or lens colour	Without cap
Light source	White LED
Bulb base	BA 9s
Light block supply	Direct 120 V
Shape of screw head	Round
Light source	LED
Operating Mode	Push-to-test
[Us] rated supply voltage	120 V
Light source colour	White
Contacts type and composition	1 C/O
Size	30 mm

Environment

Product Certifications	CSA LR25490 class 3211 03 CE UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901974161
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	2.40 in (6.1 cm)
Package 1 Length	4.49 in (11.4 cm)
Package 1 Weight	6.40 oz (181.4 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------