



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Physical

Color	Black
Depth	1.97 in (5 cm)
Height	9.45 in (24 cm)
Product Weight	5.97 lb(US) (2.71 kg)
Width	2.95 in (7.5 cm)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	5.97 lb(US) (2.71 kg)
---------------------	-----------------------

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	1.97 in (5 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------