



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Plug standard	IEC 60320 C14
Cable length	2 ft (0.61 m)
Number of cables	6

Physical

Color	Blue
Height	9.45 in (24 cm)
Width	2.76 in (7 cm)
Depth	1.57 in (4 cm)
Net Weight	1.54 lb(US) (0.7 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	10 A
Input current limits	10 A

Output

Maximum Total Current Draw per Phase	10 A
Number of power socket outlets	1 IEC 60320 C13
Cord Length	2 ft (0.61 m)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304324560
Package weight(Lbs)	1.54 lb(US) (0.7 kg)

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	1.57 in (4 cm)
Number of Units in Package 3	540

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------