



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Plug standard	IEC 60320 C20
Cable length	2 ft (0.61 m)
Number of cables	6

Physical

Color	Red
Depth	2.56 in (6.5 cm)
Height	11.81 in (30 cm)
Net Weight	2.47 lb(US) (1.12 kg)
Width	2.36 in (6 cm)

Input

Max line current	16 A
Input current limits	16 A

Output

Max current draw	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	2 ft (0.61 m)

Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient air temperature for operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304330356
Package weight(Lbs)	2.47 lb(US) (1.12 kg)

Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	2.36 in (6 cm)
Package 1 Length	2.56 in (6.5 cm)
Number of Units in Package 3	390

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------