



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	25-Node license key Server appliance User Manual Warranty card
--------------------	---

Physical

Depth	19.02 in (48.3 cm)
Height	1.73 in (4.4 cm)
Product Weight	21.05 lb(US) (9.55 kg)
Width	21.50 in (54.6 cm)

Conformance

Standards	UL 60950
-----------	----------

Environmental

Ambient Air Temperature for Operation	50...95 °F (10...35 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...90 %
Ambient Air Temperature for Storage	-31...140 °F (-35...60 °C)
Storage altitude	0...30000 ft (0.00...9144.00 m)
Storage Relative Humidity	5...95 %

Ordering and shipping details

Package weight(Lbs)	42.09 lb(US) (19.09 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.76 in (62.9 cm)
Package 1 Length	35.00 in (88.9 cm)

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------