

Product data sheet

Characteristics

AR8615

Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 6"W, Single-Sided with Door



Overview

Presentation

This 6" wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a single-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.

Lead time

Usually in Stock

Main

Provided equipment	Doors Installation guide Mounting Hardware
--------------------	--

Physical

Color	Black
Height	84.02 in (213.4 cm)
Width	5.98 in (15.2 cm)
Depth	14.17 in (36 cm)
Net Weight	59.97 lb(US) (27.2 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	UL Listed
------------------------	-----------

Ordering and shipping details

GTIN	731304291565
Package weight(Lbs)	72.97 lb(US) (33.1 kg)

Packing Units

Package 1 Height	9.80 in (24.9 cm)
Package 1 width	21.26 in (54 cm)
Package 1 Length	89.76 in (228 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------