



Overview

Presentation	This 12" wide, vertical cable manager for 2 and 4 Post open frame racks ships unassembled for rapid onsite assembly and features a full height dual hinging door and single-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.
Lead time	Usually in Stock

Main

Provided equipment	Door Installation guide Mounting Hardware
--------------------	---

Physical

Color	Black
Height	94.41 in (239.8 cm)
Width	12.01 in (30.5 cm)
Depth	11.30 in (28.7 cm)
Net Weight	22.55 lb(US) (10.23 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Ordering and shipping details

GTIN	731304300915
Package weight(Lbs)	28.06 lb(US) (12.73 kg)

Packing Units

Package 1 Height	12.28 in (31.2 cm)
Package 1 width	12.99 in (33 cm)
Package 1 Length	45.98 in (116.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
Take-back	Take-back program available
Contractual warranty	
Warranty	2 years repair or replace