

Product availability: Stock - Normally stocked in distribution facility

**Main**

Bezel material	Chromium plated metal
Control button type	Standard push-button
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Operator additional information	Without guard
Range of product	K

**Complementary**

Line Rated Current	10 A
Accessory / separate part destination	Illuminated push-button
Cap/operator or lens colour	Red
Contact operation	Standard fingersafe
Contacts type and composition	1 NO + 1 NC
Electrical connection	Screw clamp terminal
Light block supply	Via transformer 120 V AC 50/60 Hz
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Size	30 mm
Type of operator	Momentary
Utilisation category	AC-15 DC-13

**Environment**

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	UL listed file E42259 CCN NKCR CE CSA LR 25490 class 3211 03

**Ordering and shipping details**

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901849759
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5700000000000006
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------