

Product availability: Non-Stock - Not normally stocked in distribution facility



**Main**

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor

**Complementary**

Cap/operator or lens colour	Red
Contacts type and composition	Without contact block
Control type	Illuminated push-button
Light block supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz Via transformer
Mounting support	Panel
Operator position information	2 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Size	30 mm
Type of operator	Spring return right to left

**Environment**

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

**Ordering and shipping details**

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901794769
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------