

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Communication card
Range compatibility	Altivar 312 Solar Altivar 312
Communication port protocol	DeviceNet
Electrical connection	1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs 5-way screw connector, DeviceNet
Transmission rate	125 kbps, 250 kbps or 500 kbps
Number of addresses	1...63

Complementary

Input/output number	AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output
Communication service	Periodic exchange mode on outputs : polled Periodic variables ATV 312 native profile (Cia 402) 100 and 101 Periodic variables ODVA AC drive type profile 20, 21, 70 and 71 No auto device replacement Periodic exchange mode on inputs : polled, change of state, cyclic Communication monitoring can be inhibited
Display type	1 dual colour LED MNS (status)
Product weight	0.44 lb(US) (0.2 kg)

Ordering and shipping details

Category	22154 - ATV320/ATV312/ATV32 ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901838449
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35000000000000003
Returnability	N
Country of origin	SE

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0939 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------