

Product data sheet

Characteristics

GV3B11

TeSys GV3 - undervoltage trip - 110 V AC 50Hz

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	GV3B
Product or component type	Undervoltage trip
Device application	Control

Complementary

Product compatibility	GV3ME
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 50 Hz 120 V AC 60 Hz 127 V AC 50 Hz 127 V AC 60 Hz
Control circuit voltage limits	0.8...1.1 Un
[Ui] rated insulation voltage	600 V AC CSA C22.2 No 14 600 V AC UL 508 690 V AC IEC 60947-1
Threshold tripping voltage	0.7...0.35 Un
Inrush power in VA	12 VA AC
Inrush power in W	7 W DC
Hold-in power consumption in VA	7 VA AC
Hold-in power consumption in W	2.5 W DC
Operating time	10 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 2 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 1 0.75...2.5 mm ² flexible with cable end Screw clamp terminals 2 0.75...2.5 mm ² flexible with cable end Screw clamp terminals 1 0...0 in ² (1...2.5 mm ²) solid Screw clamp terminals 2 0...0 in ² (1...2.5 mm ²) solid
Tightening torque	1.2 N.m screw clamp terminals
Mechanical durability	15000 cycles
Quantity per set	Set of 10
Product weight	0.15 lb(US) (0.07 kg)

Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	00785901258094
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0723 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------