

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|---------------------------|-----------------|
| Range of product | Harmony 9001SK |
| Product or component type | Pilot light |
| Device short name | 9001SK |
| Lens type | Fresnel plastic |
| Light block supply | Direct |

Complementary

| | |
|---|--|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Shape of signaling unit head | Round |
| Cap/operator or lens colour | Red |
| Light source | Incandescent |
| Bulb base | BA 9s |
| [Us] rated supply voltage | 12...14 V AC/DC |
| Tightening torque | 7.08 lbf.in (0.8 N.m) conforming to EN/IEC 60947-1 |
| Shape of screw head | Cross slotted head |
| Connections - terminals | Screw clamp terminals (1 x 0.22...2 x 1.5 mm ²) conforming to EN/IEC 60947-1 |
| [Ith] conventional free air thermal current | 10 A |
| Short-circuit protection | 10 A cartridge fuse conforming to EN/IEC 60947-5-1 |
| [Ui] rated insulation voltage | 250 V (degree of pollution: 2) conforming to EN/IEC 60947-1 |
| [Uimp] rated impulse withstand voltage | 2.5 kV conforming to EN/IEC 60947-1 |
| Operating position | Any position |
| CAD overall width | 2.13 in (54 mm) |
| CAD overall height | 2.76 in (70 mm) |
| CAD overall depth | 1.65 in (42 mm) |
| Product weight | 0.4 lb(US) (0.181 kg) |

Environment

| | |
|---------------------------------------|--|
| Electrical shock protection class | Class II conforming to IEC 61140 |
| Protective treatment | TC |
| IP degree of protection | IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X |
| Vibration resistance | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |

| | |
|------------------------|--|
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14 |
| Product certifications | NEMA UL 508 |

Ordering and shipping details

| | |
|-----------------------|---------------------|
| Category | 21429 - 9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 00785901790822 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|