

Product data sheet

Specifications

SQUARE D



Circuit breaker, PowerPact Q, 110A, 3 pole, 240VAC, 65kA, lugs, thermal magnetic, 80%

QGL32110

Product availability: Stock - Normally stocked in distribution facility

Main

Range	PowerPact
Product name	PowerPact Q
Product or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Line Rated Current	110 A
Number of Poles	3P
Control Type	Operating handle
Breaking capacity code	G
Breaking capacity	65 kA 120/208 V AC 50/60 Hz UL 65 kA 240 V AC 50/60 Hz UL
[Ue] rated operational voltage	240 V AC 50/60 Hz UL
Network Frequency	50/60 Hz
[Uiimp] rated impulse withstand voltage	8 kV UL
Trip unit technology	Thermal-magnetic
Magnetic tripping current	2400 A
Magnetic hold current	1200 A
Continuous current rating	80 %
Utilisation category	Category A
Mechanical durability	1000 cycles loaded 5000 cycles no load
Local signalling	1 trip indicator green)
Mounting mode	Unit mount lug)
Mounting Support	Lug
Electrical connection	Lugs, load Lugs, line
Tightening torque	247.8 lbf.in (28 N.m) 0.04...0.2 in ² (25...150 mm ²) (AWG 4...300 kcmil)
Power wire stripping length	0.9 in (22 mm)
Height	6.47 in (164.34 mm)
Width	4.5 in (114.3 mm)
Depth	3.93 in (99.82 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Circuit breaker application	HACR rated
-----------------------------	------------

Environment

Standards	UL CSA NEMA NOM-003-SCFI-2000
-----------	--

Product certifications	UL CSA NOM
------------------------	------------------

Ambient Air Temperature for Operation	104...158 °F (40...70 °C)
---------------------------------------	---------------------------

Ordering and shipping details

Category	US10DE200023
----------	--------------

Discount Schedule	0DE2
-------------------	------

GTIN	785901415350
------	--------------

Returnability	Yes
---------------	-----

Country of origin	MX
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	5.56 in (14.127 cm)
------------------	---------------------

Package 1 Width	5.81 in (14.757 cm)
-----------------	---------------------

Package 1 Length	9.75 in (24.765 cm)
------------------	---------------------

Package weight(Lbs)	4.729 lb(US) (2.145 kg)
---------------------	-------------------------

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **43**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

[REACh Regulation](#) [REACh Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov**

Halogen content performance **Halogen free product**

PVC free **Yes**

Use Again

Repack and remanufacture

Circularity Profile **No need of specific recycling operations**

Take-back **No**

Technical Illustration

Dimensions

