

Product data sheet

Specifications



reversible internal door polyester 2 locks grid pattern forPLM54

NSYPAP54G

Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Front side
Range compatibility	PanelSeT PLM
Device composition	1 door 1 handle 4 fixing brackets

Complementary

Material	Polyester charged with fibreglass
Colour	Grey (RAL 7035)
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening side	Reversible (110 °)
Height	Grid pattern: 415 mm
Width	Grid pattern: 305 mm
Depth	Available depth between enclosure door : 26 mm Available depth between rear : 152 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	37.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	1.700 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	80
Package 2 Height	90.000 cm

Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	153.000 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	B8d0fb33-5e43-4121-80bd-e0d068ed5eda
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No

Image of product / Alternate images

Alternative

