

8501XMO20V04

NEMA Control Relay, Type X, master, 10A resistive at 600 VAC, 2 normally open contacts, 277 VAC 60 Hz coil



Main

Range	8501X
Relay Type	Master
Product	Relay
Current Rating	20 A AC
Contact Configuration	2 NO 2 master contact cartridges
Number of Poles	2P
Coil Voltage	277 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	UL Listed CSA CE
Operating Time	15 ms - pick-up 16 ms - drop-out

Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
GTIN	00785901018209
Nbr. of units in pkg.	1
Package weight(Lbs)	2 lb(US) (0.91 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------