



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit
Control Units	No control units
Enclosure Type	NEMA 1 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	50 Hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Number of Poles	3P
Maximum Voltage Rating	600 V AC
NEMA Size	3
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	Melting alloy
Number of Thermal Units Required	3
Disconnect Type	Fusible disconnect H, 100 A

Ordering and shipping details

Category	21293 - 8738,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	3606482142145
Nbr. of units in pkg.	1
Package weight(Lbs)	260 lb(US) (117.93 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant

Contractual warranty

Warranty	18 months
----------	-----------