



Main

Range of Product	Harmony 9001BW
Product or Component Type	Complete control station
Device short name	9001BW
Control station application	Two functions
Colour of base of enclosure	Grey

Complementary

Material	Cast aluminium
Cable entry	1 entry for 1/2" - 14 NPT
CAD overall width	2.76 in (70 mm)
CAD overall height	4.25 in (108 mm)
CAD overall depth	3.58 in (91 mm)
Type of operator	momentary
Control station composition	1 flush push-button, black, white FOR 1 flush push-button, black, white REV
Contacts type and composition	1 NO + 1 NO
Mechanical durability	5000000 cycles
[Ie] rated operational current	0.6 A 600 V, AC-1/DC-1 0.75 A 480 V, AC 1.5 A 240 V, AC 3.75 A 120 V, AC
Device mounting	Surface
Type of Installation	Indoor/outdoor

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 1 NEMA 4
Standards	EN/IEC 60947-5-5 UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-5-4 JIS C 4520 EN/IEC 60947-1
Product Certifications	CSA UL Listed
Environmental characteristic	Waterproof Dustproof

Ordering and shipping details

Category	21421-9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	785901856672
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.89 in (22.581 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	22.58 in (57.355 cm)
Package 1 Weight	3.00 lb(US) (1.361 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------