

## Product data sheet

### Characteristics

# 9001KR8P35LRRH25

Harmony 9001K, illuminated push-button, metal, mushroom 41mm, red, 30mm, 3 positions, return to center, LED red, 24-28V, 1 NC late + 1 NC



### Main

|                                 |                         |
|---------------------------------|-------------------------|
| Range of Product                | Harmony 9001K           |
| Product or Component Type       | Illuminated push-button |
| Device short name               | K                       |
| Operator additional information | Screw-on plastic        |

### Complementary

|                                |                            |
|--------------------------------|----------------------------|
| Bezel material                 | Metal                      |
| Mounting diameter              | 1.18 in (30 mm)            |
| Light source                   | LED                        |
| Bulb base                      | BA 9s                      |
| Light block supply             | Without supply             |
| Contacts type and composition  | 1 NC late break + 1 NC     |
| [Ie] rated operational current | 10 A, AC-15<br>10 A, DC-13 |
| Contact operation              | Late-break                 |
| Device presentation            | Complete product           |

### Environment

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product Certifications    | CSA LR 25490 class 3211 03<br>NEMA<br>UL listed file E42259 CCN NKCR<br>CE |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                                    |

### Ordering and shipping details

|                       |                             |
|-----------------------|-----------------------------|
| Category              | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                         |
| GTIN                  | 785901289739                |
| Nbr. of units in pkg. | 1                           |
| Package weight(Lbs)   | 8.00 oz (226.796 g)         |
| Returnability         | No                          |
| Country of origin     | MX                          |

### Packing Units

|                        |                      |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE                  |
| Package 1 Height       | 11.43 in (29.032 cm) |
| Package 1 width        | 4.50 in (11.43 cm)   |
| Package 1 Length       | 29.03 in (73.742 cm) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|