



### Main

|                              |                                                   |
|------------------------------|---------------------------------------------------|
| Range of Product             | Harmony 9001KY                                    |
| Product or Component Type    | Control station                                   |
| Device short name            | 9001KY                                            |
| Provided equipment           | Label plate HAND-OFF-AUTO                         |
| Contact block name           | KA1                                               |
| Product Specific Application | For hoisting and mechanical handling applications |
| Level or class               | Class II Division 2 Group G<br>Class III          |

### Complementary

|                                   |                                                                                                                                 |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Enclosure/cubicle description     | Wall-mounted enclosure 1 cut-out Ø 30 mm                                                                                        |
| Enclosure material                | Stainless Steel                                                                                                                 |
| Type of Installation              | Indoor/outdoor                                                                                                                  |
| Control station composition       | 1 selector switch 1 NO/1 NC                                                                                                     |
| Mechanical interlocking           | Without mechanical interlock                                                                                                    |
| Connector Type                    | Screw clamp connector                                                                                                           |
| Connections - terminals           | Direct connection AWG 2) solid stranded<br>Direct connection AWG 12) solid stranded<br>Direct connection AWG 24) solid stranded |
| [Ue] rated operational voltage    | 300 V                                                                                                                           |
| [Ie] rated operational current AC | 10 A                                                                                                                            |

### Environment

|                                       |                                                                |
|---------------------------------------|----------------------------------------------------------------|
| NEMA degree of protection             | NEMA 13<br>NEMA 3<br>NEMA 1<br>NEMA 4                          |
| Environmental characteristic          | Resistant against immersion in water<br>Dust and oil resistant |
| Product Certifications                | UL Listed                                                      |
| Ambient Air Temperature for Operation | -13...140 °F (-25...60 °C)                                     |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                     |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1                         |
| GTIN              | 785901040071                |
| Returnability     | No                          |
| Country of origin | MX                          |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 12.70 in (32.258 cm)   |
| Package 1 Width              | 5.00 in (12.7 cm)      |
| Package 1 Length             | 32.26 in (81.935 cm)   |
| Package 1 Weight             | 2.65 lb(US) (1.202 kg) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|