

Product data sheet

Characteristics

9001SKR3B

Push-button head, Harmony 9001SK, plastic, projecting, black, 30mm, spring return



Main

| | |
|---------------------------|----------------------|
| Range of Product | Harmony 9001SK |
| Product or Component Type | Head for push-button |
| Device short name | 9001SK |

Complementary

| | |
|-------------------------------|---|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Shape of signaling unit head | Octagonal |
| Light source | without |
| Light block supply | Without supply |
| Contacts type and composition | Without contact block |
| Product Certifications | CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR |
| IP degree of protection | IP64 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Cap/operator or lens colour | Black |
| Operator profile | Projecting |
| Type of operator | Spring return |
| Size | 30 mm |

Ordering and shipping details

| | |
|-------------------|-------------------|
| Category | 21429-9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 785901856344 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.62 in (19.355 cm) |
| Package 1 Width | 3.00 in (7.62 cm) |
| Package 1 Length | 19.35 in (49.161 cm) |
| Package 1 Weight | 1.60 oz (45.359 g) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or operator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|