



### Main

|                           |  |
|---------------------------|--|
| Range of Product          | Harmony 9001KY                           |
| Product or Component Type | Control station                          |
| Device short name         | 9001SK                                   |
| Level or class            | Class III<br>Class II Division 2 Group G |

### Complementary

|                                   |                       |
|-----------------------------------|-----------------------|
| Type of Installation              | Indoor/outdoor        |
| Connector Type                    | Screw clamp connector |
| [Ue] rated operational voltage    | 600 V                 |
| [Ie] rated operational current AC | 10 A                  |

### Environment

|                                       |  |
|---------------------------------------|--|
| NEMA degree of protection             | NEMA 1<br>NEMA 3<br>NEMA 13<br>NEMA 4                          |
| Environmental characteristic          | Dust and oil resistant<br>Resistant against immersion in water |
| Ambient Air Temperature for Operation | -13...140 °F (-25...60 °C)                                     |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                     |

### Ordering and shipping details

|                   |                   |
|-------------------|-------------------|
| Category          | 21429-9001 SK,SKY |
| Discount Schedule | CS1               |
| GTIN              | 785901546733      |
| Returnability     | No                |
| Country of origin | MX                |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Number of Units in Package 1 | 1                   |
| Package 1 Height             | 2.54 in (6.452 cm)  |
| Package 1 Width              | 1.00 in (2.54 cm)   |
| Package 1 Length             | 6.45 in (16.387 cm) |
| Package 1 Weight             | 1.76 oz (49.895 g)  |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           |  <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information |  Yes  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|