



Main

Main Input Voltage	AC 3 phase
Provided Equipment	Installation guide Integrated network management Network Management Card User Manual

General

Compressor Type	Scroll
Air Discharge Patterns	Upflow
Intake Air	Top Return
Piping Material	Copper

Physical

Height	61.18 in (155.4 cm)
Width	39.41 in (100.1 cm)
Depth	39.41 in (100.1 cm)
Net Weight	600.01 lb(US) (272.16 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Number of Power Feeds	2
Input Frequency	50/60 Hz

Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

Ordering and shipping details

GTIN	731304410232
Nbr. of units in pkg.	1
Package weight(Lbs)	672.41 lb(US) (305 kg)

Packing Units

Unit Type of Package 1	BOX
Package 1 Height	44.72 in (113.6 cm)
Package 1 width	42.72 in (108.5 cm)
Package 1 Length	68.70 in (174.5 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---