



## Overview

Lead time	Usually in Stock
-----------	------------------



## Main

Main Input Voltage	200 V 208 V
Plug standard	NEMA L15-30P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Provided Equipment	Installation guide Safety guide

## Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	15.28 in (38.8 cm)
Depth	4.96 in (12.6 cm)
Net Weight	7.94 lb(US) (3.6 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Input

Line Rated Current	24 A
Acceptable Input Voltage	200...240 V
Max line current	30 A
Input current limits	30 A
Load Capacity	8600 VA
Input Frequency	50/60 Hz

## Output

Number of power socket outlets	3 IEC 60320 C19
--------------------------------	-----------------

## Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

## Ordering and shipping details

GTIN	731304327837
Package weight(Lbs)	11.16 lb(US) (5.06 kg)

## Packing Units

Package 1 Height	13.07 in (33.2 cm)
Package 1 width	17.91 in (45.5 cm)
Package 1 Length	7.68 in (19.5 cm)
Number of Units in Package 3	30

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------