



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	3 phase
Main Output Voltage	120 V 208 V
Plug standard	NEMA L21-20P
Number of rack unit	0U
Cable length	3 ft (0.91 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit

Physical

Color	Black
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Depth	1.73 in (4.4 cm)
Net Weight	12.04 lb(US) (5.46 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	5700 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	21 NEMA 5-20R 6 NEMA L6-20R
--------------------------------	--------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	CUL Listed UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304207924
Package weight(Lbs)	14.02 lb(US) (6.36 kg)

Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------