



## Overview

Presentation	Basic Rack PDU 14.4 kW solution for high density installations
Lead time	Usually in Stock

## Main

Main Input Voltage	3 phase
Main Output Voltage	208 V
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit

## Physical

Color	Black
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Depth	3.74 in (9.5 cm)
Net Weight	21.74 lb(US) (9.86 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

## Input

Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365

## Output

Number of power socket outlets	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Conformance

Product Certifications	CUL Listed CSA METI Denan UL Listed
Standards	UL 60950

## Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304240761
Package weight(Lbs)	30.47 lb(US) (13.82 kg)

## Packing Units

Package 1 Height	80.98 in (205.7 cm)
Package 1 width	3.11 in (7.9 cm)
Package 1 Length	12.24 in (31.1 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------