

Product data sheet

Characteristics

AP8706S-NAX590

Power Cord Kit (6 ea), Locking, C13 to C14, 1.8M (6ft), North America, Blue



Overview

Lead time Usually in Stock

Physical

Color	Blue
Height	9.45 in (24 cm)
Width	2.95 in (7.5 cm)
Depth	2.17 in (5.5 cm)
Net Weight	2.98 lb(US) (1.35 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304326403
Package weight(Lbs)	2.98 lb(US) (1.35 kg)

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	2.17 in (5.5 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------