



Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

Main

Input Connection Type	IEC 60320 C14
Cable length	6 ft (1.83 m)
Number of cables	6

Physical

Color	Black
Height	9.45 in (24 cm)
Width	2.95 in (7.5 cm)
Depth	2.17 in (5.5 cm)
Net Weight	2.98 lb(US) (1.35 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	10 A
Input current limits	10 A

Output

Maximum Total Current Draw per Phase	10 A
Number of power socket outlets	1 IEC 60320 C13
Cord Length	6 ft (1.83 m)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304294405
Package weight(Lbs)	2.98 lb(US) (1.35 kg)

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	2.17 in (5.5 cm)
Number of Units in Package 3	300

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------