

Product data sheet

Characteristics

AP8716R

Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.8m



Overview

Presentation

Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time

Usually in Stock

Main

Plug standard	IEC 60320 C20
Cable length	6 ft (1.83 m)
Number of cables	6
Provided Equipment	3 Left-angle jumper cords 3 Right-angle jumper cords

Physical

Color	Black
Height	11.81 in (30 cm)
Width	3.15 in (8 cm)
Depth	2.76 in (7 cm)
Net Weight	4.76 lb(US) (2.16 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	16 A
Input current limits	16 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	6 ft (1.83 m)

Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304279716
Package weight(Lbs)	4.76 lb(US) (2.16 kg)

Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	2.76 in (7 cm)
SCC14	10731304279713
Number of Units in Package 3	240

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------