



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Cable length	6 ft (1.83 m)
Color	Black
Depth	1.73 in (4.4 cm)
Height	70.51 in (179.1 cm)
Product Weight	13.98 lb(US) (6.34 kg)
Width	2.20 in (5.6 cm)

Input

Input Frequency	50/60 Hz
Plug standard	NEMA L21-20P
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	2 NEMA 5-20R 36 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	---

Conformance

Standards	CSA C22.2 No. 60950 UL 60950-1
-----------	-----------------------------------

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Liquid Electrolyte Value	0

Ordering and shipping details

GTIN	00731304322443
Package weight(Lbs)	17.57 lb(US) (7.97 kg)

Packing Units

Package 1 Height	78.74 in (200 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.21 in (10.7 cm)
Number of Units in Package 3	48

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------