

Product data sheet

Characteristics

AP940-1525A

UPS Communications Cable Smart Signalling 15' / 4.5m - DB9 to RJ45



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Connector B	SUB-D 9 female Smart Signaling
Height	2.24 in (5.7 cm)
Cable length	15 ft (4.57 m)
Connector A	RJ45 male
Depth	4.25 in (10.8 cm)
Net Weight	0.44 lb(US) (0.2 kg)
Width	8.74 in (22.2 cm)

Output

Number of port	1
----------------	---

Ordering and shipping details

GTIN	00731304310822
Package weight(Lbs)	0.44 lb(US) (0.2 kg)

Packing Units

Package 1 Height	2.24 in (5.7 cm)
Package 1 width	8.74 in (22.2 cm)
Package 1 Length	4.25 in (10.8 cm)
SCC14	10731304310829

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Take-back

Take-back program available
