

# Product data sheet

## Characteristics

# AP9563

Rack PDU, Basic, 1U, 20A, 120V, (10)5-20;  
5-20P



### Overview

Lead time	Usually in Stock
-----------	------------------



### Main

Main Input Voltage	100 V 120 V
Main Output Voltage	120 V
Plug standard	NEMA 5-20P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets

### Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Depth	2.24 in (5.7 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

### Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	1920 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	10 NEMA 5-20R
--------------------------------	---------------

### Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

## Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304203889
Package weight(Lbs)	8.02 lb(US) (3.64 kg)

## Packing Units

Package 1 Height	2.76 in (7 cm)
Package 1 width	18.27 in (46.4 cm)
Package 1 Length	9.02 in (22.9 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	 <a href="#">REACh Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------