



Overview

Presentation	The Step-Down Transformer converts high voltage (208 or 200 VAC) output into low voltage (120 or 100 VAC) output for powering low voltage AC equipment.
Lead time	Usually in Stock

General

Provided Equipment	User Manual Rack Mounting brackets
--------------------	---------------------------------------

Physical

Color	Black
Depth	24.02 in (61 cm)
Height	3.50 in (8.9 cm)
Product Weight	95.20 lb(US) (43.18 kg)
Width	17.52 in (44.5 cm)

Input

Permissible voltage	208 V
Max line current	24 A
Input current limits	30 A
Load Capacity	5000 VA
Plug standard	NEMA L6-30P
Nominal Input Voltage	208 V

Output

Max current draw	24 A
Number of power socket outlets	12
Efficiency	90 %
Number of power socket outlets	12 NEMA 5-20R
Output voltage	120 V

Conformance

Product Certifications	CSA
Standards	OSHPD UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304249139
Package weight(Lbs)	110.23 lb(US) (50 kg)

Packing Units

Package 1 Height	10.00 in (25.4 cm)
Package 1 width	24.49 in (62.2 cm)
Package 1 Length	37.52 in (95.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------