

Product data sheet

Characteristics

AP9804

UPS Communications Cable Smart Signalling 15' / 4.5m



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Cable length	15 ft (4.57 m)
Number of cables	1
Product Compatibility	UPS

Physical

Color	Black
Net Weight	0.99 lb(US) (0.45 kg)
Mounting Location	Front
Mounting Mode	Not rack-mountable
Connector B	SUB-D 9 male Smart Signaling
Connector A	SUB-D 9 female Smart Signaling

Output

Number of port	1
----------------	---

Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

Ordering and shipping details

GTIN	731304203001
Package weight(Lbs)	0.99 lb(US) (0.45 kg)

Packing Units

Package 1 Height	9.02 in (22.9 cm)
Package 1 width	4.02 in (10.2 cm)
Package 1 Length	2.01 in (5.1 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------