



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Input Connection Type	NEMA L21-20P
Number of rack unit	0U
Number of cables	1

Physical

Color	Black
Net Weight	2.25 lb(US) (1.02 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Max line current	20 A
Input current limits	20 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	3 NEMA L6-20R
Cord Length	2 Ft (0.61 m) 4 Ft (1.22 m) 6 ft (1.83 m)

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	32...113 °F (0...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304198802
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.99 in (7.6 cm)
Package 1 Width	12.52 in (31.8 cm)
Package 1 Length	12.52 in (31.8 cm)
Package 1 Weight	3.00 lb(US) (1.36 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------