



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	DC
Battery Type	Lead-Acid battery
Provided Equipment	Installation guide

Physical

Color	Black
Height	4.13 in (10.5 cm)
Width	5.94 in (15.1 cm)
Depth	2.56 in (6.5 cm)
Net Weight	6.61 lb(US) (3 kg)
Mounting Mode	Not rack-mountable

Output

Battery Capacity	9.4 Ah
------------------	--------

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	Non-condensing 0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	12 V
RBC Quantity	1

Ordering and shipping details

GTIN	731304346869
Package weight(Lbs)	7.72 lb(US) (3.5 kg)

Packing Units

Package 1 Height	3.50 in (8.9 cm)
Package 1 width	6.89 in (17.5 cm)
Package 1 Length	8.39 in (21.3 cm)
SCC14	10731304346866
Number of Units in Package 3	240

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------