



Overview

Presentation	An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	24U
Provided equipment	Casters Doors Key(S) Leveling feet Roof Side Panels

Physical

Height	47.19 in (119.85 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	196.41 lb(US) (89.09 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304261889
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	52.05 in (132.2 cm)
Package 1 Width	29.37 in (74.6 cm)
Package 1 Length	45.51 in (115.6 cm)
Package 1 Weight	235.50 lb(US) (106.82 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------