

Product data sheet

Characteristics

AR3107W

APC NetShelter SX, Server Rack Enclosure,
48U, White, 2258H x 600W x 1070D mm



Overview

| | |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

Main

| | |
|----------------------------|--|
| Number of rack unit | 48U |
| Provided equipment | Baying hardware Documentation CD Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels |
| Color | White |
| Height | 88.90 in (225.8 cm) |
| Width | 23.62 in (60 cm) |
| Depth | 42.13 in (107 cm) |
| Net Weight | 304.75 lb(US) (138.23 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Maximum Mounting Depth | 36.02 in (91.49 cm) |
| Minimum Mounting Depth | 7.52 in (19.1 cm) |
| Rack Width | 19" |
| Marking | 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels |
| Permanent permissible load | 2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static |

Physical

| | |
|----------------------------|---|
| Color | White |
| Height | 88.90 in (225.8 cm) |
| Width | 23.62 in (60 cm) |
| Depth | 42.13 in (107 cm) |
| Net Weight | 304.75 lb(US) (138.23 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Maximum Mounting Depth | 36.02 in (91.49 cm) |
| Minimum Mounting Depth | 7.52 in (19.1 cm) |
| Rack Width | 19" |
| Marking | 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels |
| Permanent permissible load | 2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static |

Conformance

| | |
|-----------|----------------------|
| Standards | UL 60950 EIA-310E |
|-----------|----------------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

| | |
|---------------------|---------------------------|
| GTIN | 731304323242 |
| Package weight(Lbs) | 347.63 lb(US) (157.68 kg) |

Packing Units

| | |
|------------------------------|---------------------|
| Package 1 Height | 93.90 in (238.5 cm) |
| Package 1 width | 29.61 in (75.2 cm) |
| Package 1 Length | 47.99 in (121.9 cm) |
| Number of Units in Package 3 | 1 |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|