

Product data sheet

Characteristics

AR3812

APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, without Sides, Roofs, Doors, Black, 1991H x 600W x 806D mm



Overview

Presentation	Feature-rich enclosure specifically for the professional A/V market and optimized for cable management, power distribution, and airflow management.
Lead time	Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Baying hardware Documentation CD Installation guide Leveling feet Mounting Hardware Pre-installed casters

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	31.73 in (80.6 cm)
Net Weight	151.33 lb(US) (68.64 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	26.73 in (67.89 cm)
Rack Width	19"
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304284123
Package weight(Lbs)	182.39 lb(US) (82.73 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	83.50 in (212.1 cm)
Package 1 width	29.49 in (74.9 cm)
Package 1 Length	40.51 in (102.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------