

# Product data sheet

## Characteristics

AR7306

NetShelter AV 42U 825mm Deep Split Side Panels Qty (2)



### Overview

Lead time      Usually in Stock

### Main

Provided equipment	Installation guide Key(S) Slam Latches
--------------------	--

### Physical

Color	Black
Height	32.76 in (83.2 cm)
Width	28.39 in (72.1 cm)
Depth	0.51 in (1.3 cm)
Net Weight	20.04 lb(US) (9.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Ordering and shipping details

GTIN	731304279563
Package weight(Lbs)	35.08 lb(US) (15.91 kg)

### Packing Units

Package 1 Height	37.01 in (94 cm)
Package 1 width	32.01 in (81.3 cm)
Package 1 Length	7.76 in (19.7 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

---

RoHS exemption information

Yes

Take-back

Take-back program available

---

**Contractual warranty**

---

Warranty

2 years repair or replace

---