

Product data sheet

Characteristics

AR8606

APC NetShelter Cable Management, Horizontal Cable Manager, 2U, Single Side with Cover, Black, 482.6 x 88.9 x 165.1 mm



Overview

Presentation	High density 2U, 6-in (150-mm) deep, horizontal cable manager with cover. Features cable tie-off and cable access slots in the backplate for front to back cable pass-through.
Lead time	Usually in Stock

Main

Number of rack unit	2U
Provided equipment	Double-sided Cable Manager configuration hardware Installation guide Mounting Hardware

Physical

Color	Black
Height	3.50 in (8.89 cm)
Width	19.00 in (48.26 cm)
Depth	6.50 in (16.51 cm)
Net Weight	2.20 lb(US) (1 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Conformance

Product Certifications	TAA compliance
------------------------	----------------

Ordering and shipping details

GTIN	731304291541
Package weight(Lbs)	2.76 lb(US) (1.25 kg)

Packing Units

Package 1 Height	6.00 in (15.24 cm)
Package 1 width	20.50 in (52.07 cm)
Package 1 Length	7.87 in (20 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------